


Unique on demand

Configurator for hydraulic cylinders

LIEBHERR

Components




Configure
your hydraulic
cylinder now



Configure series- production ranges




Configure
your hydraulic
cylinder now



380 bar

Highly dynamic and mobile applications of earth movement


The hydraulic cylinders of the series-production range 380 bar come in handy mainly in mobile applications. This also means that they can be used wherever durable and robust products are required in highly dynamic situations. The “eye-eye mounting” was specially designed for connection to construction machinery and thus ensures optimal operation. The hybrid cylinder option is an added bonus. The use of carbon-fibre reinforced plastic saves on weight and increases machine efficiency.



260 bar

Mobile and stationary applications

The hydraulic cylinders of the 260 bar series-production range can be used under demanding conditions of static and dynamic loads. A wide range of mounting types are available, including alternative oil connections and piston rod designs. The hydraulic cylinder adapts to fit your application.



ISO 6022

Mechanical and plant engineering

The hydraulic cylinders according to ISO 6022 come in handy in stationary applications, in which they can withstand equally with static and dynamic loads. The hydraulic cylinders can be equipped with a large portfolio of additional intelligent options (e.g. position transducer, end position cushioning or proximity switch) as required.

Ready, set, configure

For the first time, Liebherr has made it possible to individually and easily configure all hydraulic cylinder series-production ranges via an online-based configurator on the company's website. Depending on the application and requirements, the configurator offers all kinds of variations: from the 380 bar series for mobile applications, the ISO 6022 series for industrial use all the way to the 260 bar series as a link between mobile and stationary applications.

"When it comes to selecting and assembling the right product, the configurator offers assistance through stored logic and targeted user guidance." explains Jan Winter, product manager at Liebherr-Components Kirchdorf GmbH.



Available at any time
on all devices,
location-independent



CRP-hybrid cylinders
configurable for
380 bar



Offer received
within one
business day




Wide range
wavailable for
many applications



Product key:
Recall and saving is
possible at any time



3D models and
technical data
for download



Request your individually suitable offer now.


Components

From A to Z – the components division of the Liebherr Group offers a broad range of solutions in the area of mechanical, hydraulic, electric and electronic drive system and control technology. The efficient components and systems are produced at a total of ten production sites around the world to the highest standards of quality. Central contact persons for all product lines are available to our customers at

Liebherr-Components AG and the regional sales and distribution branches.

Liebherr is your partner for joint success: from the product idea to development, manufacture and commissioning right through to customer service solutions like remanufacturing.

components.liebherr.com



LIEBHERR

Liebherr-Components AG · Post box 222 · 5415 Nussbaumen, Switzerland
+41 56 296 43 00 · components@liebherr.com · www.liebherr.com

Subject to change
COK-01-10/2022_EN