

Heavy Lift Handling in Rostock

TCC 78000

Litronic®



LIEBHERR

TCC 78000

Litronic®

Characteristics

The rail mounted heavy lift crane TCC 78000 moves over 420 metres on a portal between the Liebherr-MCCtec Rostock GmbH factory site and the adjacent quayside. Equipped with a double trolley (two rails per side) and a rail gauge of 30 metres, the gantry crane provides optimum flexibility for handling all types of large-sized and heavy goods.




Customer Benefits

- Handling by experienced operating and service personnel
- Optimal positioning of the cargo due to size of the gantry
Gantry: 17 m clearance, 30 m track gauge
- Designed for travelling with load
- Loading and unloading of vessels with a draught of up to 10.80 m possible
- Unobstructed view to the load
- Strategically well-placed land and sea connections

Specifications

| | |
|--|-------------------|
| Max. lifting capacity: | 1,600 t |
| Main hoist: | 1,600 t at 36 m |
| Auxiliary hoist 1: | 250 t at 99 m |
| Auxiliary hoist 2: | 25 t at 105 m |
| Max. lifting height main hoist: | 112 m at R = 34 m |
| Max. lifting height auxiliary hoist 2: | 158 m at R = 22 m |
| Slewing range: | 360° |
| Drive system: | Electro-hydraulic |



Industries

- Offshore industry
- Shipbuilding industry
- Industrial plant construction
- Logistics industry
- Heavy loads sector

Liebherr-MCCtec Rostock GmbH

Liebherrstraße 1, D-18147 Rostock/GERMANY
Tel.: +49 381 6006 5800
www.liebherr.com, E-Mail: heavylifthandling@liebherr.com
www.facebook.com/LiebherrMaritime