

Offshore Crane Technology
Liebherr MTC Series



LIEBHERR

Liebherr MTC Series



Applications

General oil & gas Industry

Characteristics

Safe and reliable king post mounted offshore crane with rope luffing system and lattice boom.

Specifications

Overturning moment:	1900 tm - 6000 tm
Main hoist capacity:	15 t - 150 t
Boom length:	30 m - 72 m
Slewing range:	360° unlimited
Drive system:	Electro- or diesel-hydraulic

Customer Benefits

- Maintenance-friendly
- Minimised total lifecycle costs
- Guaranteed spare parts availability
- Worldwide customer service station network

Authorities | Rules | Certificates



Other capacities, authorities, rules, certificates and information upon request

Offshore Crane Customer References*

ADCO | ADMA-OPCO | AGIP | ALMAZ | APACHE | BP | BW OFFSHORE | CANADIAN COAST GUARD | CHEVRON | CNOOC | COASTLINE | CONOCOPHILLIPS | COSCO | COSL | COTEMAR DALIAN | DBB JACK-UP | DEEPOCEAN | DIAMOND | DOLPHIN | DRYDOCKS WORLD | DSME | ENSCO | EQUINOX | ESSAR | EXXON MOBIL | FLOATEL | FRIGSTAD | GDF SUEZ | GSI GULF PIPING | HANDEL MARITIME | HESS | HGO | HOCHTIEF | HOOP LOBITH | HUSKY | HYUNDAI | INPEX | JAYA | JURONG | KEPPEL | LAMPRELL | LUKOIL | MAERSK | McDERMOTT MODEC | MUSTANG | NEXEN | NOBLE | NORDIC YARDS | NPCC | OCEANOGRAFIA | ODEBRECHT | ODFJELL | PAXOCEAN | PEMEX | PETROBRAS | PETROFAC | PETROSERV | POET | PROSAFE REPSOL | ROSETTI MARINO | ROWAN | RWE | SAIPEM | SAMSUNG | SAUDI ARAMCO | SBM | SEADRAGON | SEADRILL | SEAJACKS | SEMBawang | SEVAN | SHELL | SMIT | SONGA | STATOIL SUBSEA7 | SWIBER | TALISMAN | TECHNIP | TEEKAY | TIDEWATER | TOTAL | TRANSOCEAN | VAN OORD | VANTAGE | WINTERSHALL | WORKFOX | WORLEY PARSONS | YANTAI RAFFLES | extract only*

Liebherr-MCCtec Rostock GmbH

Liebherrstraße 1, D-18147 Rostock/GERMANY
 Tel.: +49 381 6006 5020
 www.liebherr.com, E-Mail: offshore.crane@liebherr.com
 www.facebook.com/LiebherrMaritime