

Offshore Crane Technology

Liebherr RL Series



LIEBHERR

Liebherr RL Series



Applications

General oil & gas industry

Characteristics

Safe and reliable slew bearing offshore crane with cylinder luffing system and box boom.

Specifications

Overturning moment: 650 tm - 4200 tm
 Main hoist capacity: 8 t - 100 t
 Boom length: 18 m - 54 m
 Slewing range: 360° unlimited
 Drive system: Electro- or diesel-hydraulic

Customer Benefits

Maintenance-friendly
 Minimised total lifecycle costs
 Guaranteed spare parts availability
 Worldwide customer service station network

Authorities | Rules | Certificates



Other capacities, authorities, rules, certificates and information upon request

Offshore Crane Customer References*

ADCO | ADMA-OPCO | AGIP | ALMAZ | APACHE | BP | BW OFFSHORE | CANADIAN COAST GUARD | CHEVRON | CNOOC | COASTLINE | CONOCOPHILLIPS | COSCO | COSL | COTEMAR
 DALIAN | DBB JACK-UP | DEEPOCEAN | DIAMOND | DOLPHIN | DRYDOCKS WORLD | DSME | ENSCO | EQUINOX | ESSAR | EXXON MOBIL | FLOATEL | FRIGSTAD | GDF SUEZ | GSI
 GULF PIPING | HANDEL MARITIME | HESS | HGO | HOCHTIEF | HOOP LOBITH | HUSKY | HYUNDAI | INPEX | JAYA | JURONG | KEPPEL | LAMPRELL | LUKOIL | MAERSK | McDERMOTT
 MODEC | MUSTANG | NEXEN | NOBLE | NORDIC YARDS | NPCC | OCEANOGRAFIA | ODEBRECHT | ODFJELL | PAXOCEAN | PEMEX | PETROBRAS | PETROFAC | PETROSERV | POET | PROSAFE
 REPSOL | ROSETTI MARINO | ROWAN | RWE | SAIPEM | SAMSUNG | SAUDI ARAMCO | SBM | SEADRAGON | SEADRILL | SEA JACKS | SEMBawang | SEVAN | SHELL | SMIT | SONGA | STATOIL
 SUBSEA7 | SWIBER | TALISMAN | TECHNIP | TEEKAY | TIDEWATER | TOTAL | TRANSOCEAN | VAN OORD | VANTAGE | WINTERSHALL | WORKFOX | WORLEY PARSONS | YANTAI RAFFLES | extract only*