


Request Data

Hydraulic Cylinders

General Information

Request Date:	Telephone:
Company:	E-Mail:
Contact Person:	Application:
Road:	Machine / Type:
Postcode: Location:	Required quantity:
Country:	Requested delivery date:

Load Specification



Type of Cylinder

Differential cylinder Synchronised cylinder


Max. operating pressure: bar

Stroke Frequency: 1/min

Operating Temperature: (-20°C to +80°C)

Fluid:

Hydraulic Cylinder Installation Position



Approx. Load Cycles:

Min. Operation Time: oh


Ambient Temperature: °C °F

Fluid Temperature: °C °F

Mounting Types



MT4 Trunnion mounting



MF3 Flange mounting at cylinder head



MF4 Flange mounting at base



Basic form without mounting



MP3 Bushing at bottom



MP5 spherical bearing a.b.



MS2 Foot Mounting



Spherical bearings, both ends

