




D-88427 Bad Schussenried  
 Thomas Maier  
 phone: + 49(0)7583/949-414  
 Fax: + 49(0)7583/949-399  
 email: [thomas.maier@liebherr.com](mailto:thomas.maier@liebherr.com)  
[www.water-content-measurement.com](http://www.water-content-measurement.com)

## LIEBHERR-Litronic- SoftFMS II



### LITRONIC- SoftFMS II

#### NOTES

- simple integration of LIEBHERR-moisture measuring system in customer software
- max. 16 measuring channels
- parameterization and calibration via Litronic-FMSII PC-Software
- fully-automatic operation
- channel bundeling, coarse-/fine - change over
- adjustable measurement range
- material curve change-over
- mounting of FMSII-Dongle on standard mounting-rail TS35 for simple switch cabinet mounting

#### TECHNICAL DATA

##### FMS II-DLL

Evaluation measuring cycle: up to 60 measurements per second  
 Measured output value: via FMS II-DLL-API  
 Measuring range : 0 %-100 % rel. moisture

Operation types : (range adjustable)  
Batch process, continuous process  
System requirements: PC with Microsoft Windows (Windows 95, 98 2000, XP),  
Ethernet-Interface

FMS II-DONGLE

Supply voltage: 12..30 V DC, max. 315mA (12V)  
Ethernet: 10/100M, RJ45, 1,5 kV magn. Isolation  
Sensorbus: RS 485, Multiprocessor record, 15 kV ESD-protection  
size: 90 x 100,4 x 22mm (incl. fixing flaps)  
weight: 140g  
working temperature: 0..55 °C