

Liebherr A 922 Rail Litronic at Conexpo Con/Agg 2020 construction trade show

- Operating weight 45,000 - 51,600 lb (20. 4 - 23. 4 t)
- Can be operated either on road or rail
- Decades of experience in developing and producing railroad excavators

Las Vegas (USA), 10 March 2020 – Liebherr is presenting the new A 922 Rail Litronic at the Conexpo Con/Agg 2020 trade show. The new machine is available in both the Final Tier 4 and Stage IIIA (compliant) exhaust emissions standards. Because it is a railroad machine, the A 922 Rail is suitable for use on railway tracks and for road construction and is fast thanks to the mobile undercarriage. A rail travel drive is mounted on both sides of the undercarriage. When entering the rails, the rail travel drive lifts the tires to rail height. The inside wheels of the dual tires ensure travel of the excavator on the tracks.

With the A 922 Rail, Liebherr is offering the perfect overall package: the basic machine, the rail travel drive, the quick coupler system, attachments and all of the safety systems are developed by Liebherr and perfectly customized for the machine. Liebherr has been developing and producing railroad excavators for rail construction since 1967 and is a global market leader in this segment as an OEM manufacturer.

New generation guarantees greater efficiency

The new generation of Liebherr railroad excavators impresses with the higher level of efficiency. The new 120 kW / 161 HP engine ensures that the A 922 Rail achieves even higher working speeds with the usual fluid equipment movements. The innovative hydraulic concept of the A 922 Rail consists of a Liebherr variable displacement double pump with independent control circuits. High-performance, hydraulic attachments can be operated independently of the working and travel movements of the Liebherr railroad excavator. The delivery rate of the proven Liebherr variable displacement double pump was increased to 2 x 220 l/min for even better performance. The heavy ballast was also redesigned to yield the best bearing load values with improved weight distribution and a more compact rear dimension of 6.6 ft (2,000 mm).

Service-orientated machine design

The service-orientated machine design of the A 922 Rail guarantees short maintenance times and minimises the associated maintenance costs thanks to the time savings. All maintenance points are easily accessible from the ground. The new generation has simplified access to important components even further; for example, air, oil and fuel filters, the main battery switch, the central lubrication point for the undercarriage and the pilot valves for the hydraulic system are much easier to access.

Comfortable double cab

The spacious double cab featuring standard roll over protective structure (ROPS) and a modern interior design offers the best conditions for comfortable, focused and productive work. Entrance lighting is provided to make accessing the cab easier. The usual generous use of glass and standard rear and side cameras provide an exceptional view of the working area and swing range. The touch-screen color display used for display and operation purposes, as well as the other control elements on the console and comfortable driver's seat are all perfectly matched to one another to form the perfect unit.

Safety systems directly from the manufacturer

Occupational safety is extremely important in track construction. Liebherr offers safety systems which are perfectly tailored to the machine requirements. The safety technologies include load torque, height and sway limitation and the virtual wall.

Liebherr undercarriage for use on tracks worldwide

The A 922 Rail is available with various undercarriage versions with different track widths and rail wheels, which make it possible to use it on tracks worldwide. An independent variable displacement pump for the rail travel drive provides the best traction and safe propulsion at all times. Standard integrated brakes in the rail wheel shorten the braking distance in both the lowered and elevated position and enhance safety.

Higher levels of productivity thanks to Liebherr attachments and Liebherr quick coupling system

The A 922 Rail has many different areas of application thanks to the broad range of Liebherr attachments. To improve productivity even further, the railroad excavator can be fitted with an optional, fully hydraulic quick coupling system developed by Liebherr. The hydraulic quick coupler system combined with an automatic, hydraulic coupling system enable a quick and secure change of mechanical and hydraulic attachments from the cab. This can increase productivity by 30% on average.

Captions

liebherr-a-922-rail-litronic-1.jpg

The multitasking construction machine: The Liebherr A 922 Rail Litronic railroad excavator is used both in rail construction and for traditional earthmoving operations.

liebherr-a-922-rail-litronic-2.jpg

Liebherr's fully hydraulic quick coupling system increases the productivity of the A 922 Rail Litronic significantly: This makes it possible to change attachments quickly and securely from the cab at the touch of a button.

Contact person

Nadine Willburger

Marketing

Phone: +49 7354 80-7332

E-mail: nadine.willburger@liebherr.com

Published by

Liebherr-Hydraulikbagger GmbH

Kirchdorf an der Iller/Germany

www.liebherr.com