

Offshore Crane Technology

# Liebherr BOS Series



**LIEBHERR**

# Liebherr BOS Series



## Applications

General oil & gas industry  
 Heavy lift construction & maintenance  
 Offshore wind plant installation & maintenance

## Characteristics

Safe and reliable slew bearing offshore crane with rope luffing system and lattice boom.

## Specifications

Overturning moment: 2600tm - 45000tm  
 Main hoist capacity: 25t - 1200t  
 Boom length: 30m - 102m  
 Slewing range: 360° unlimited  
 Drive system: Electro- or diesel-hydraulic

## Customer Benefits

Maintenance-friendly  
 Minimised total lifecycle costs  
 Guaranteed spare parts availability  
 Worldwide customer service station network

## Offshore Crane Customer References\*

ADCO | ADMA-OPCO | AGIP | ALMAZ | APACHE | BP | BW OFFSHORE | CANADIAN COAST GUARD | CHEVRON | CNOOC | COASTLINE | CONOCOPHILLIPS | COSCO | COSL | COTEMAR DALIAN | DBB JACK-UP | DEEPOCEAN | DIAMOND | DOLPHIN | DRYDOCKS WORLD | DSME | ENSCO | EQUINOX | ESSAR | EXXON MOBIL | FLOATEL | FRIGSTAD | GDF SUEZ | GSI GULF PIPING | HANDEL MARITIME | HESS | HGO | HOCHTIEF | HOOP LOBITH | HUSKY | HYUNDAI | INPEX | JAYA | JURONG | KEPPEL | LAMPRELL | LUKOIL | MAERSK | McDERMOTT MODEC | MUSTANG | NEXEN | NOBLE | NORDIC YARDS | NPCC | OCEANOGRAFIA | ODEBRECHT | ODFJELL | PAXOCEAN | PEMEX | PETROBRAS | PETROFAC | PETROSERV | POET | PROSAFE REPSOL | ROSETTI MARINO | ROWAN | RWE | SAIPEM | SAMSUNG | SAUDI ARAMCO | SBM | SEADRAGON | SEADRILL | SEAJACKS | SEMBawang | SEVAN | SHELL | SMIT | SONGA | STATOIL SUBSEA7 | SWIBER | TALISMAN | TECHNIP | TEEKAY | TIDEWATER | TOTAL | TRANSOCEAN | VAN OORD | VANTAGE | WINTERSHALL | WORKFOX | WORLEY PARSONS | YANTAI RAFFLES | extract only\*

## Authorities | Rules | Certificates



Other capacities, authorities, rules, certificates and information upon request.

## Liebherr-MCCtec Rostock GmbH

Liebherrstraße 1, D-18147 Rostock/GERMANY  
 Tel.: +49 381 6006 5020  
 www.liebherr.com, E-Mail: offshore.crane@liebherr.com  
 www.facebook.com/LiebherrMaritime