

Offshore Crane Technology

Liebherr CAL Series



LIEBHERR

Liebherr CAL Series



Applications

Heavy lift construction & maintenance
Wind plant installation & maintenance

Characteristics

Safe and reliable state-of-the-art Crane Around the Leg with slewing bearing technology, rope luffing system and lattice twin boom.

Specifications

Overturning moment: 45000tm - 64000tm
Main hoist capacity: 1200t - 1700t
Boom length: up to 108m
Slewing range: $\pm 460^\circ$
Drive system: Electro-hydraulic

Customer Benefits

Maintenance-friendly
Minimised total lifecycle costs
Guaranteed spare parts availability
Customer Service Stations - worldwide

Offshore Crane Customer References*

ADCO | ADMA-OPCO | AGIP | ALMAZ | APACHE | BP | BW OFFSHORE | CANADIAN COAST GUARD | CHEVRON | CNOOC | COASTLINE | CONOCOPHILLIPS | COSCO | COSL | COTEMAR DALIAN | DBB JACK-UP | DEEPOCEAN | DIAMOND | DOLPHIN | DRYDOCKS WORLD | DSME | ENSCO | EQUINOX | ESSAR | EXXON MOBIL | FLOATEL | FRIGSTAD | GDF SUEZ | GSI GULF PIPING | HANDEL MARITIME | HESS | HGO | HOCHTIEF | HOOP LOBITH | HUSKY | HYUNDAI | INPEX | JAYA | JURONG | KEPPEL | LAMPRELL | LUKOIL | MAERSK | McDERMOTT MODEC | MUSTANG | NEXEN | NOBLE | NORDIC YARDS | NPCC | OCEANOGRAFIA | ODEBRECHT | ODFJELL | PAXOCEAN | PEMEX | PETROBRAS | PETROFAC | PETROSERV | POET | PROSAFE REPSOL | ROSETTI MARINO | ROWAN | RWE | SAIPEM | SAMSUNG | SAUDI ARAMCO | SBM | SEADRAGON | SEADRILL | SEAJACKS | SEMBawang | SEVAN | SHELL | SMIT | SONGA | STATOIL SUBSEA7 | SWIBER | TALISMAN | TECHNIP | TEEKAY | TIDEWATER | TOTAL | TRANSOCEAN | VAN OORD | VANTAGE | WINTERSHALL | WORKFOX | WORLEY PARSONS | YANTAI RAFFLES | extract only*

Authorities | Rules | Certificates



Other capacities, authorities, rules, certificates and information upon request.

Liebherr-MCCtec Rostock GmbH

Liebherrstraße 1, D-18147 Rostock/GERMANY
Tel.: +49 381 6006 5020
www.liebherr.com, E-Mail: offshore.crane@liebherr.com
www.facebook.com/LiebherrMaritime